

## Ultrasonic coating thickness measurement

## QuintSonic



### Measurement of:

- paint, plastics, enamel and other insulating coatings
- applied on wood, plastics, glass, ceramics and on metals
- wall thickness of plastics and metals through the coating

**New: Measurement of a multi-layer system  
in only one measuring process**

## Application

The new portable gauge was especially designed for non-destructive coating thickness measurement of paint, varnish, plastics and other insulation coatings applied on wood, plastics, glass, ceramics etc. as well as for polymer layers on metals. As a special feature, the gauge offers the possibility to measure the total thickness as well as the individual layers of a multi-layer system in only one measuring process. The robust gauge is appropriate for use in the laboratory, in production and on site.

## Measuring Procedure

When the probe is placed on the coated surface, it sends sound pulses which penetrate the coating through to the base material. Provided the coatings and the substrate possess different acoustic properties, these pulses are reflected by the different surfaces and transmitted to the transducer in the probe. The various time intervals are measured and calculated by a microprocessor to give individual and total coating thickness. The time to obtain a reading is approx. two seconds or less. If the portable MiniPrint printer is con-



Thickness measurement of a double-layer coating applied on wood

## Technical data

<b>Field of applications and measuring ranges:</b>	<b>Single layers:</b>	<b>10 µm ... 500 µm</b>
	<b>Multi-layers:</b>	<b>max 500 µm total coating thickness</b>
	<b>Wall thickness of metals:</b>	<b>0.1 ... 8 mm</b>
	<b>Wall thickness of plastics:</b>	<b>0.2 ... 3 mm</b>
<b>Resolution:</b>	<b>1 µm</b>	
<b>Measuring uncertainty &lt; 100 µm</b>	<b>± (2 µm + 3 %*)</b>	
<b>Measuring uncertainty &gt; 100 µm</b>	<b>± (2 µm + 2 %*)</b> (*of reading)	
<b>Memory capacity:</b>	<b>max. 10,000 measuring values in max. 500 batches</b>	
<b>Statistical evaluation:</b>	<b>n, <math>\bar{x}</math>, s, kvar, max, min, with time and date of print-out and reading</b>	
<b>Limit setting:</b>	<b>with optical and acoustic warning when limits are exceeded</b>	
<b>Interface:</b>	<b>RS 232 C for MiniPrint data printer</b>	
<b>Power supply:</b>	<b>2,4 V akkupack: 2 x 1,2 V AA NiMH or NiCd (approx. 2,500 measurements)</b>	
<b>Charger:</b>	<b>90 V ~ to 264 V (charging time: 4 hours)</b>	
<b>Dimensions/weight:</b>	<b>Gauge: 150 mm x 82 mm x 35 mm/150 g, Probe 30 mm x 45 mm dia.</b>	
<b>Ambient temperature:</b>	<b>-15 °C ... +55 °C</b>	

nected all readings and statistical data can be printed out in individual memories and batches.

## Description

This new portable non-destructive coating thickness gauge has been developed for the easy and quick measurement of coatings on non-metallic materials which up to now could only be done destructively. The gauge will also measure paint coatings on a metal base.

## Supply schedule

- Gauge conforming to DIN EN ISO 2808, ASTM D6132, with probe and rechargeable batteries
- Charger
- Operating instructions
- Plastic case
- Coupling liquid, 100 g
- Software Qsoft
- RS 232 connection cable

## Recommended accessories

- Portable printer MiniPrint
- Rubber protection case with mounting device (neck cord optional)
- Belt case set – two cases of different size for gauge and accessories
- Carrying case for gauge and printer MiniPrint



# ElektroPhysik

**ElektroPhysik**  
 Pasteurstr. 15  
 D-50735 Köln  
 Tel.: +49 (0) 221 75204-0  
 Fax: +49 (0) 221 75204-67  
 www.elektrophysik.com  
 info@elektrophysik.com

**ElektroPhysik USA**  
 770 West Algonquin Rd.  
 Arlington Heights IL 60005  
 Phone: +1 847 437-6616  
 Fax: +1 847 437-0053  
 www.elektrophysik.com  
 epusa@elektrophysik.com

**ElektroPhysik Nederland**  
 Borgharenweg 140  
 6222 AA Maastricht  
 Tel.: +31(0)43/3 52 06 60  
 Fax: +31(0)43/3 63 11 68  
 www.elektrophysik.com  
 epnl@elektrophysik.com

**ElektroPhysik Belgium**  
 Allée Marie Louise 4b  
 4121 Neupré  
 Tél.: +32(0)4 336 52 05  
 Fax: +32(0)4 338 01 80  
 www.elektrophysik.com  
 epbe@elektrophysik.com